

# **Active color Yellow King**

## - ACYK & Series -


MODEL ACYK-5 $\alpha$  MODEL ACYK-10 $\alpha$  MODEL ACYK-20

– ACYK-GRα Series –

MODEL ACYK-5GR $\alpha$  MODEL ACYK-10GR $\alpha$  MODEL ACYK-20GR

# Corresponding with contamination! Air blow is standard equipment.

- Superior cost performance and noiseless elevator for 2nd sorting built-in!
- •Improved simplify of maintenance and operability!
- Now it's possible to install the magnet for metal removable (Option)
- Black and red rice sorting function can be installed! (Option)
- •All operation can be done by one touch at front panel!!





MODEL ACYK-10a

Complex adjustment is easy to operate with easily viewable waveform monitor.

Auto waveform adjustment function is equipped!




It has 3 kinds of sorting pattern. The pattern can be changed as usage by one touch operation.

### [Outline drawings]

#### ACYK-5 $\alpha$ /5GR $\alpha$ /10 $\alpha$ /10GR $\alpha$

#### $ACYK-20\alpha/20GR\alpha$



#### (Specification)

Model		ACYK-5α	ACYK-5GRα	ACYK-10α	ACYK-10GRα	ACYK-20α	ACYK-20GRα
061	1st sorting	4	4	8	8	16	16
Channel	2nd sorting	1	1	2	2	4	4
Main power		AC200V 1.5A	AC200V 2.5A	AC200V 2.5A	AC200V 5A	AC200V 5A	AC200V 6.5A
Compressor Capacity		0.4Kw	0.4Kw	0.75Kw	0.75Kw	1.5Kw	1.5Kw
Dust cleaner capacity		-	_		,		
Piping (inch)		3/8	3/8	3/8	3/8	3/8	3/8
Maximum Throughput		0.4t/h	0.4t/h	0.8t/h	0.8t/h	1.6t/h	1.6t/h
Main use		Colored grain is sorted from cleaned rice (GR type: colored glass plastic stone and so on) Chalky and Glutinous rice is sorted from cleaned rice (GR type: Chalky glass plastic stone and so on) Nonglutinous rice is sorted from Glutinous rice and chalky (GR Type:chalky glass plastic stone and so on)  **Please ask to a dealer for details about brown rice, wheat and buckwheat					

- \* Air compressor, air drier and dust cleaner are optional parts.
- ※ Air compressor capacity and dust cleaner capacity will change by materials.
- \*Process capacity changes with the state of material and sorting
- \* Outward form and specification may be changed without a prior notice for improvement.



Manufactured by

Active K.T. CO., LTD.

3-9-15 Minami-chou, Chuo-ku, Chiba-City Chiba 260-0842

OTIDA 200 0042

TEL:043-300-7830 FAX:043-266-1452

Sales by

Active Marketing CO., LTD.

2-22-13 Minami-chou, Chuo-ku, Chiba-City

Chiba 260-0842

TEL:043-300-7831 FAX:043-266-1462

URL: http://activecorp.co.jp/